

# PROJET® MJP 3600 DENTAL

High throughput MultiJet Printing production of precision wax-ups and models



## ProJet MJP 3600 Dental


<b>Printing Modes</b> UHD Mode HDX Mode HDP Mode	Ultra High Definition High Definition Smooth (drill guides, jaw models and orthodontic thermoforming models) High Definition Plaster (plaster-like appearance for crown and bridge, partial denture and orthodontic models)
<b>Net Build Volume (xyz)*</b> UHD Mode HDX Mode HDP Mode	11.75 x 7.2 x 8 in (298 x 183 x 203 mm) 11.75 x 7.2 x 8 in (298 x 183 x 203 mm) 11.75 x 7.2 x 8 in (298 x 183 x 203 mm)
<b>Resolution (xyz)</b> UHD Mode HDX Mode HDP Mode	750 x 750 x 890 DPI; 29 μ layers 375 x 450 x 790 DPI; 32 μ layers 375 x 450 x 790 DPI; 32 μ layers
<b>Accuracy (typical)</b>	±0.001-0.002 inch per inch (0.025-0.05 mm per 25.4 mm) of part dimension. Accuracy may vary depending on build parameters, part geometry and size, part orientation, and post-processing.
<b>Build Materials</b> UHD Mode HDX Mode HDP Mode	VisiJet M3 Dentcast VisiJet M3 Dentcast, VisiJet M3 Stoneplast, VisiJet M3 PearlStone VisiJet M3 Dentcast, VisiJet M3 Stoneplast, VisiJet M3 PearlStone
<b>Support Material</b>	VisiJet S300
<b>Material Packaging</b>	Build and support materials in clean 4.41 lbs (2 kg) bottles (printer holds up to 2 of each with auto-switching)
<b>Electrical</b>	100-127 VAC, 50/60 Hz, single-phase, 15A 200-240** VAC, 50 Hz, single-phase, 10A
<b>Dimensions (WxDxH)</b> 3D Printer Crated 3D Printer Uncrated	32.5 x 56.3 x 68.5 in (826 x 1430 x 1740 mm) 29.5 x 47 x 59.5 in (749 x 1194 x 1511 mm)
<b>Weight</b> 3D Printer Crated 3D Printer Uncrated	955 lbs (433 kg) 659 lb (299 kg)
<b>ProJet® Accelerator Software</b>	Easy build job set-up, submission and job queue management; Automatic part placement and build optimization tools; Part stacking and nesting capability; Extensive part editing tools; Automatic support generation; Job statistics reporting tools
<b>E-mail Notice Capability</b>	Yes
<b>Network Compatibility</b>	Network ready with 10/100 Ethernet interface
<b>Client Hardware Recommendation</b>	1.8 GHz with 1GB RAM (OpenGL support 64 mb video RAM) or higher
<b>Client Operating System</b>	Windows® XP Professional, Windows Vista, Windows 7
<b>Input Data File Formats Supported</b>	STL and SLC
<b>Post-Processing</b>	ProJet Finisher for easy removal of eco-friendly wax supports
<b>Operating Temperature Range</b>	64-82 °F (18-28 °C)
<b>Noise</b>	< 65 dBa estimated (at medium fan setting)
<b>5-Year Printhead Warranty</b>	Standard
<b>Certifications</b>	CE

\* Maximum part size is dependent on geometry, among other factors.

\*\* Requires small external transformer supplied by 3D Systems in the provided country kit.

# VISIJET® M3 DENTAL MATERIALS

For castable and pressable wax-ups and precision dental models



Properties	Condition	VisiJet M3 Dentcast	VisiJet M3 PearlStone	VisiJet M3 Stoneplast	VisiJet S300
Composition			UV Curable Plastic		Wax Support Material
Color		Dark Green	White	Natural	White
Bottle Quantity		2 kg	2 kg	2 kg	2 kg
Density @ 80 °C (liquid)	ASTM D4164	102 g/cm <sup>3</sup>	104 g/cm <sup>3</sup>	102 g/cm <sup>3</sup>	N/A
Tensile Strength	ASTM D638	32 MPa	40 MPa	41 MPa	N/A
Tensile Modulus	ASTM D638	1724 MPa	1794 MPa	1850 MPa	N/A
Elongation at Break	ASTM D638	12.3%	7.7%	17%	N/A
Flexural Strength	ASTM D790	45 MPa	N/A	51 MPa	N/A
Heat Distortion Temperature	ASTM D648 @ 0.45 MPa	N/A	88 °C	56 °C	N/A
Ash Content		0.01%	N/A	N/A	N/A
Melting Point		N/A	N/A	N/A	60 °C
Softening Point		N/A	N/A	N/A	40 °C
USP Class VI Certified*		No	No	Yes	N/A
Printing Modes Compatibility		UHD, HDX, HDP	HDX, HDP	HDX, HDP	UHD, HDX, HDP
Description		Wax-up castable material	Solid stone appearance	Translucent or stone finish**	Non-toxic wax material for hands- free melt-away supports

\* DISCLAIMER: It is the responsibility of each customer to determine that its use of any VisiJet® material is safe, lawful and technically suitable to the customer's intended applications. The values presented here are for reference only and may vary. Customers should conduct their own testing to ensure suitability for their intended application.

\*\* Choice of finish requires additional post processing.

**MANUFACTURING THE FUTURE™**

[www.3dsystems.com](http://www.3dsystems.com)



**USA**  
Tel: +1 803.326.3900  
**UK**  
Tel: +44 1442 282 600

**Germany, Scandinavia, Eastern Europe, Middle East**  
Tel: +49 6151 357 0

**Asia-Pacific**  
Melbourne Tel: +61 3 9819 4422  
Sydney Tel: +61 2 9516 5571

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, material combined with, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2016 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. The 3D Systems logo, ProJet and VisiJet are registered trademarks of 3D Systems, Inc.